

FDM TPU 92A

[FDM® TPU 92A](#) is a thermoplastic polyurethane with a Shore A value of 92. The material exhibits high elongation, superior toughness, durability and abrasion resistance.

FDM TPU 92A brings the benefits of elastomers to [FDM 3D printing](#) and offers the capability to quickly produce large and complex elastomer parts. Typical applications include flexible hoses, tubes, air ducts, seals, protective covers and vibration dampeners.

FDM TPU 92A is available on the [F123™ Series 3D Printers](#) and is compatible with QSR™ soluble support material.

Mechanical Properties	Test Method	Value	
		XY Orientation	XZ Orientation
Shore Hardness (molded)	ASTM D2240	92 Shore A	92 Shore A
Tensile Strength, Yield (Type 1, 0.125", 0.2"/min)	ASTM D412	15.6 MPa (2,265 psi)	16.1 MPa (2,332 psi)
Tensile Strength, Ultimate (Type 1, 0.125", 0.2"/min)	ASTM D412	16.8 MPa (2,432 psi)	17.4 MPa (2,519 psi)
Tensile Modulus (Type 1, 0.125", 0.2"/min)	ASTM D412	15.3 MPa (2,212 psi)	20.7 MPa (3,000 psi)
Elongation at Break (Type 1, 0.125", 0.2"/min)	ASTM D412	552%	482%
Elongation at Yield (Type 1, 0.125", 0.2"/min)	ASTM D412	466%	385%
Tensile Stress at 100% Elongation (PSI)	ASTM D412	6.9 MPa (999 psi)	7.6 MPa (1,096 psi)
Tensile Stress at 300% Elongation (PSI)	ASTM D412	11.0 MPa (1,598 psi)	11.9 MPa (1,722 psi)
Flexural Strength (Method 1, 0.05"/min)	ASTM D790	1.8 MPa (255 psi)	2.4 MPa (351 psi)
Flexural Modulus (Method 1, 0.05"/min)	ASTM D790	25.6 MPa (3,719 psi)	36.9 MPa (5,349 psi)
Flexural Strain at Break (Method 1, 0.05"/min)	ASTM D790	No break	No break
Tear Strength - Stamped	ASTM D624-C	84.6 N/mm (483 lbF/in)	NA
Compressive Strength, Yield (Method 1, 0.05"/min)	ASTM D695	2.6 MPa (384 psi)	2.6 MPa (384 psi)
Compressive Strength, Ultimate (Method 1, 0.05"/min)	ASTM D695	2.6 MPa (384 psi)	2.6 MPa (384 psi)
Compressive Modulus (Method 1, 0.05"/min)	ASTM D695	16.9 MPa (2,457 psi)	16.9 MPa (2,457 psi)
Compression Set at 22 Hours @ 23 °C	ASTM D395	21%	NA
Compression Set at 22 Hours @ 70 °C	ASTM D395	44%	NA

FDM TPU 92A

Thermal Properties	Test Method	Value
Heat Deflection (HDT) @ 66 psi	ASTM D648	38 °C (100.4 °F)
Heat Deflection (HDT) @ 15 psi	NA	56 °C (132.8 °F)
Vicat Softening Temperature (Rate B/50)	ASTM D1525	95 °C (203 °F)
Glass Transition Temperature (Tg)	DMA (SSYS)	-42 °C (-43.6 °F)
Coefficient of Thermal Expansion (x-direction)	ASTM E831	139 µm/(m·°C) (7.72E-05 in/(in·°F))
Coefficient of Thermal Expansion (y-direction)	ASTM E831	159 µm/(m·°C) (8.83E-05 in/(in·°F))
Coefficient of Thermal Expansion (z-direction)	ASTM E831	176 µm/(m·°C) (9.78E-05 in/(in·°F))

Electrical Properties	Test Method	Value	
		XY Orientation	XZ Orientation
Volume Resistivity	ASTM D257	6.09E+10 ohm-cm	7.17E+13 ohm-cm

Other	Test Method	Value
Specific Gravity	ASTM D792	1.13502
Flame Classification	UL94	HB* and V2**

* HB: Slow burning on a horizontal specimen; burning rate < 76 mm/min for thickness < 3 mm or burning stops before 100 mm.

** V-2: Burning stops within 30 seconds on a vertical specimen; drips of flaming particles are allowed.

Stratasys Headquarters

7665 Commerce Way,
Eden Prairie, MN 55344
+1 800 801 6491 (US Toll Free)
+1 952 937-3000 (Intl)
+1 952 937-0070 (Fax)

stratasys.com
ISO 9001:2008 Certified

1 Holtzman St., Science Park,
PO Box 2496
Rehovot 76124, Israel
+972 74 745 4000
+972 74 745 5000 (Fax)

